



REVERSE - PRESSURE TEST PLUG

Dimensions

Equipment Weight - (kg).....: 1
 Lifting/ Transportation.....: Transportation on pallet

Construction year

Built.....: 2015

Area of use / certification

Onshore/offshore.....: Offshore

Type

Item type.....: Grip Tight Reverse Plug
 Fabricator.....: Curtiss Wright
 Model.....: GTRP-1P80

Flow / Pressure / Volume

P-max (bar).....: 155
 P-max (PSI).....: 2250
 Nominal Pipe Size (Inches).....: 1.00
 Nominal Pipe Schedule.....: 80
 Plug Outside Ø (mm).....: 0.8
 Clearance with pipe (mm).....: 3.0
 Plug Length (mm).....: 476

Additional information

Equipment / Functions.....: Maximum Upstream Pressure: 103 barg
 Operational Temperature Range: -23^o C thru 82^o C
 Compatible Test Media: Water, Air, Glycol (Low Temperature Applications)

Installation:
 Use GTRP installation tool when installing plug.
 Normal Installation Torque : 16 Nm
 Maximum Installation Torque : 22 Nm
 Compression Nut HEX Size: 9/16"

Eliminate concerns over inadequate joint strength when pressure testing welded flange connections. Previous flange weld testing devices have been shown to apply only radial and hoop stresses to the weld location. Use of these devices for pressure testing will not adequately test or verify the longitudinal strength of the flange-to-pipe weld.

- The plug and test flange act independently of each other so that the weld joint is subjected to real world stresses during pressure testing
- Flange to pipe welds are tested without needing to pressurize the entire system
- Available for pipe sizes ranging from 2" to 12" (DN50 - DN300). Larger sizes available upon request.

FEATURES & BENEFITS:

- Real World Service Conditions – Provides a solution where the weld joint is subjected to 100% of the hydrotest stress – radial, hoop and longitudinal Test simulates.
- Sizes from 2" through 14" NPS from stock – larger or smaller sizes available.
- High Performance – Working pressures to 2,250 psig (154 Barg) - higher pressures available
- Safer – Uses proven GripTight – self gripping action
- Reduce Cost – Uses a minimal amount of water per test